



Actual

**Catalog Number:** SCG-M404  
**Product ID:** 7TCA303040R0037  
**UPC Number:** 78621015867  
**EAN Number:** 05415022429725  
**Status:** Active

Non Armoured Cable Gland, Thread Size M40, Cable Range 22 to 32 Millimeters, Thread Length 9 Millimeters, Stainless Steel

- Low profile compact cable glands
- Wide cable clamping range
- Excellent corrosion resistance
- Ideal for wet locations

### North American Specifications (UNSPSC)

UNSPSC	39121431 Cable gland connector
IGCC	4601 Cable gland connector
Brand Name	T&B
Type	Non Armoured Cable Gland
Application	General purpose, Panel building, Light fixture and housings
Standard	cULus, RoHS, WEEE, LVD
Size	M40
Conductor Range	22 to 32 Millimeters
Material	316 Stainless Steel
Color	Metallic
NEMA Rating	NEMA 4
Temperature Rating	-20 to +100 Degrees C

### European Specifications (ETIM)

ETIM	EC000441 Cable screw gland
Thread type	Metric
Nominal thread size metric/PG	40
Pitch thread	1.5mm
Thread length	9mm
Suitable for cable diameter	22 - 32mm
Material	Metal
Material quality	Stainless steel V4A
Surface protection	Untreated
Degree of protection (IP)	IP68
Colour	Natural colour
Model	Straight
Operating temperature	-20-+100°C

### Packaging

Inner Quantity	5
Inner Dimensions (inches)	7.09x3.54x3.54
Outer Quantity	10
Outer Dimensions (inches)	3.94x15.75x11.02
Weight Uom	0.02 lbs. Each

### Documents / Support Tools

Technical Drawing / Data Sheet	TDS000032
Technical Drawing / Data Sheet Canada	TDS000032
Instruction Sheet	TA05283-TB2
Support/Tools	Available on Website

Thomas & Betts - USA