



**Catalog Number:** SP-NPT1-B  
**Product ID:** 7TAD105980R0047  
**UPC Number:** 78621090892  
**Status:** A



Actual

Spiral Cable/Cord Fitting with Intergral Strain-Relief, Trade Size 1 Inch, Cable Range 0.709 to 0.984 Inch, IP68 Rating, Polyamide 6 Body and Cap, Neoprene Sealing Ring, Black

#### North American Specifications (UNSPSC)

UNSPSC	39121431 Cable gland connector
IGCC	4601 Cable gland connector
Type	Cord/Cable Fittings
Special Features	Meets VDE ratings for European Applications
Application	Ideal in Environments Where Maximum Protection is Needed Against Conductor Fatigue Caused by Flexing Cables
Standard	UL
Size	1 Inch
Conductor Range	0.709 to 0.984 Inch
Material	Polyamide/Nylon 6
Color	Black
NEMA Rating	4
Temperature Rating	-30 to +80 C

#### European Specifications (ETIM)

ETIM	EC000441 Cable screw gland
Thread type	NPT
Nominal thread size inch/gas pipe thread	1 inch
Thread length	18.01mm
Suitable for cable diameter	18.0086-24.9936mm
Material	Plastic
Material quality	Polyamide (PA)
Degree of protection (IP)	IP68
Colour	Black
Model	Straight
Operating temperature	-30-+80°C

#### Packaging

Outer Quantity	50
Outer Dimensions (inches)	20.62x15.18x14.37
Weight Uom	14.35 lbs. per 100

#### Documents / Support Tools

Technical Drawing / Data Sheet	WSD-000010
--------------------------------	------------