



**Catalog Number:** SP-NPT34-G  
**Product ID:** 7TAD105330R0003  
**UPC Number:** 78621090889  
**Status:** A



Actual



Representative

Spiral Cable/Cord Fitting with Intergral Strain-Relief, Trade Size 3/4 Inch, Cable Range 0.512 to 0.709 Inch, IP68 Rating, Polyamide 6 Body and Cap, Neoprene Sealing Ring, Grey

- Strain-relief is integral to the fitting, saving time and costs of additional parts for cable/cord installations.

#### North American Specifications (UNSPSC)

UNSPSC	39121431 Cable gland connector
IGCC	4601 Cable gland connector
Type	Cord/Cable Fittings
Special Features	Meets VDE ratings for European Applications
Application	Ideal in Environments Where Maximum Protection is Needed Against Conductor Fatigue Caused by Flexing Cables
Standard	UL E13938
Size	3/4 Inch
Conductor Range	0.512 to 0.709 Inch
Material	Polyamide/Nylon 6
Color	Gray
NEMA Rating	4
Temperature Rating	-30 to +80 C

#### European Specifications (ETIM)

ETIM	EC000441 Cable screw gland
Thread type	NPT
Nominal thread size inch/gas pipe thread	3/4 inch
Thread length	14.99mm
Suitable for cable diameter	13.0048-18.0086mm
Material	Plastic
Material quality	Polyamide (PA)
Degree of protection (IP)	IP68
Colour	Light grey
Model	Straight
Operating temperature	-30-+80°C

#### Packaging

Outer Quantity	100
Outer Dimensions (inches)	20.62x15.18x14.37
Weight Uom	9 lbs. per 100

#### Documents / Support Tools

Technical Drawing / Data Sheet	WSD-000010
--------------------------------	------------

#### Header

3D Model	Available on Website
----------	----------------------