



Catalog Number: SP-NPT38-B
Product ID: 7TAD105330R0004
UPC Number: 78621090886
Status: A



Actual



Representative

Spiral Cable/Cord Fitting with Intergral Strain-Relief, Trade Size 3/8 Inch, Cable Range 0.197 to 0.394 Inch, IP68 Rating, Polyamide 6 Body and Cap, Neoprene Sealing Ring, Black

North American Specifications (UNSPSC)

UNSPSC	39121431 Cable gland connector
IGCC	4601 Cable gland connector
Type	Cord/Cable Fittings
Special Features	Meets VDE ratings for European Applications
Application	Ideal in Environments Where Maximum Protection is Needed Against Conductor Fatigue Caused by Flexing Cables
Standard	UL E13938
Size	3/8 Inch
Conductor Range	0.197 to 0.394 Inch
Material	Polyamide/Nylon 6
Color	Black
NEMA Rating	4
Temperature Rating	-30 to +80 C

European Specifications (ETIM)

ETIM	EC000441 Cable screw gland
Thread type	NPT
Nominal thread size inch/gas pipe thread	3/8 inch
Thread length	14.99mm
Suitable for cable diameter	5.0038-10.0076mm
Material	Plastic
Material quality	Polyamide (PA)
Degree of protection (IP)	IP68
Colour	Black
Model	Straight
Operating temperature	-30-+80°C

Packaging

Outer Quantity	250
Outer Dimensions (inches)	20.62x15.18x14.37
Weight Uom	3.63 lbs. per 100

Documents / Support Tools

Technical Drawing / Data Sheet	WSD-000010
--------------------------------	------------

Header

3D Model	Available on Website
----------	----------------------