



Catalog Number: SP20/M20/B
Product ID: 7TCA296020R0153
UPC Number: 78621024778
EAN Number: 05020963000003
Status: A



Representative

1/2 Inch Nickel Plated Brass Straight Fitting with Swivel External Thread, Metric Thread Size M20

North American Specifications (UNSPSC)

UNSPSC	39121311 Electrical fittings
IGCC	4441 Electrical fittings
Type	Conduit Fitting with Metric Threads
Application	For Insertion into Threaded Entries or Knockout to Connect Conduit
Size	1/2 Inch
Material	Brass
Finish	Nickel Plated
Color	Metallic
Cable Entry	M20 Thread

European Specifications (ETIM)

ETIM	EC001180 Screw connection for protective metallic hose
Nominal diameter	20mm
Degree of protection (IP) conduit dependant	IP54-IP54
Model	Straight
Revolving thread	Y
Construction type	External thread
Connection type screw connection to housing	Thread
Thread type	Metric
Thread connection size	M20 x 1.5
One-piece	Y
Material housing	Brass
Surface protection	Nickel-plated
Thread length	10mm
Total length	33.9mm
Approved in combination with protective conduit DIN EN 61386-23	N
Approved in combination with protective conduit CSA	N
Approved in combination with protective conduit UL	N
Approved in combination with protective conduit FI	N
Operating temperature	-50-+350°C

Packaging

Inner Quantity	10
Inner Dimensions (inches)	6x1x10
Outer Quantity	300
Outer Dimensions (inches)	14x14x6
Weight Uom	13.42 lbs. per 100

Header

3D Model	Available on Website
----------	----------------------

