




Representative



Line Art

Catalog Number: ST100-469SPVC
Product ID: 7TBA051140R0005
UPC Number: 78621030893
EAN Number: 05415022459708
Status: A

Star Teck steel jacketed fitting PVC coated. Hub size of 1 inch. Range over jacket from 1.187 - 1.375 inch.

A natural extension of the 10464 Series, the first STAR TECK cable fitting incorporated input from end-users in Canadian industry and was the first teck fitting to use a "pop-on" design requiring no disassembly. Other unique features included a splined gland and gripping features. The original STAR TECK fitting for teck and ACWU cable set the standard for ease of installation, quality engineering and safe, reliable terminations in challenging industrial environments.

- Built-in O-Ring provides 360 degree seal even when enclosure surface is rough or uneven.
- Sharp Biting Teeth provide superior electrical bonding and allow corrosive liquids to drain away quickly.
- Watertight Tapered bushing. Cone shaped to provide a secure, tight fit while eliminating cupping or water in vertical installations.
- Easy to Install in Tight Spaces Low profile gland nut fits tight spaces. Has grooves for screwdriver installation, and flats for a wrench. Durable and reusable with funnel entry for easy cable insertion.

North American Specifications (UNSPSC)

UNSPSC	39121311 Electrical fittings
IGCC	4441 Electrical fittings
Type	Teck Cable Fittings
Standard	UL E38947, CSA 23086, CSA 4484
Size	1 inch
Material	Steel
Finish	PVC Coated
Color	Black

Packaging

Outer Quantity	10
Outer Dimensions (inches)	8.75x8.9x5.25
Weight Uom	105 lbs. per 100

Documents / Support Tools

Technical Drawing / Data Sheet	TDS000037
Technical Drawing / Data Sheet US	Available on Website
Catalog Page	Available on Website
Catalog Page	Available on Website
Instruction Sheet	TA02187-TB2
Support/Tools	Available on Website
Catalog Canada	Available on Website