




Representative



Line Art

Catalog Number: ST250-478SPVC
Product ID: 7TBA051140R0014
UPC Number: 78620989603
EAN Number: 05415022461114
Status: Active

Steel fitting with a hub size of 2-1/2 inches and will handle outer jacket diameters from 2.58 to 2.84 inches. PVC coated.

A natural extension of the 10464 Series, the first STAR TECK cable fitting incorporated input from end-users in Canadian industry and was the first teck fitting to use a "pop-on" design requiring no disassembly. Other unique features included a splined gland and gripping features. The original STAR TECK fitting for teck and ACWU cable set the standard for ease of installation, quality engineering and safe, reliable terminations in challenging industrial environments.

- Built-in O-Ring provides 360 degree seal even when enclosure surface is rough or uneven.
- Sharp Biting Teeth provide superior electrical bonding and allow corrosive liquids to drain away quickly.
- Watertight Tapered bushing. Cone shaped to provide a secure, tight fit while eliminating cupping or water in vertical installations.
- Easy to Install in Tight Spaces Low profile gland nut fits tight spaces. Has grooves for screwdriver installation, and flats for a wrench. Durable and reusable with funnel entry for easy cable insertion.

North American Specifications (UNSPSC)

UNSPSC	39121311 Electrical fittings
IGCC	4441 Electrical fittings
Brand Name	T&B Fittings
Type	Teck Cable Fittings
Standard	UL E38947, CSA 23086, CSA 4484
Size	2-1/2 inches
Material	Steel
Finish	PVC Coated
Color	Black

Packaging

Inner Quantity	1
Outer Quantity	5
Outer Dimensions (inches)	11.93x11.93x6.12
Weight Uom	600 lbs. per 100

Documents / Support Tools

Technical Drawing / Data Sheet	TDS000037
Technical Drawing / Data Sheet US	Available on Website
Technical Drawing / Data Sheet Canada	Available on Website
Instruction Sheet	TA00904-TB2
Catalog Canada	Available on Website