



Representative

**Catalog Number:** T75MCG  
**Product ID:** 7TAD013210R0089  
**UPC Number:** 78620986871  
**Status:** A

3/4 Inch Series 35 Unipak Type T Conduit Body, Cover and Gasket, Body Material and Finish Malleable Iron Zinc Plated with Aluminum, Acrylic Coating, Cover Material and Finish Stamped Steel Zinc Plated, Gasket Material Neoprene

- All threaded hubs have tapered threads.
- Suitable for use in concrete
- Serve as pulling outlets during conductor installation
- Provide easy access for splices in branch conductors
- Make 90 degree bends in conduit runs
- Act as mounting outlets for wiring devices and lighting fixtures
- Provide access to conductors for maintenance and future system changes

#### North American Specifications (UNSPSC)

UNSPSC	39131708 Electrical conduit fitting body
IGCC	5563 Electrical conduit fitting body
Type	Series 35 Unipak Conduit Body, Cover & Gasket
Special Features	Zinc-Plated Iron Construction with Aluminum Acrylic Coating Provides Durability, Impact Resistance and Corrosion Resistance.
Application	To Connect Conduit Sections
Standard	UL E2969
Hub Size	3/4 in
Material	Malleable Iron
Finish	Zinc Plating with Aluminum Acrylic Coating

#### Packaging

Outer Quantity	10
Outer Dimensions (inches)	13x6.75x5.5
Weight Uom	1.41 lbs. Each

#### Documents / Support Tools

Technical Drawing / Data Sheet	WSD-000301
--------------------------------	------------