



Representative

Catalog Number: TB200M
Product ID: 7TAD013210R0096
UPC Number: 78621096091
Status: A

Series 35 Thru-Feed with Bottom Tap 2 Inch Conduit Body, Body Material Malleable Iron, Finish Zinc Plating with an Aluminum, Acrylic Coating for Use with Rigid/IMC Conduit

- Features tapered, threaded NPT hubs.
- Covers available in iron or stamped steel, both zinc-plated and supplied with stainless steel captive screws.
- Suitable for use in concrete.
- Serve as pulling outlets during conductor installation
- Provide easy access for splices in branch conductors
- Make 90 degree bends in conduit runs
- Act as mounting outlets for wiring devices and lighting fixtures
- Provide access to conductors for maintenance and future system changes

North American Specifications (UNSPSC)

UNSPSC	39131708 Electrical conduit fitting body
IGCC	5563 Electrical conduit fitting body
Type	Series 35 Conduit Body
Special Features	Zinc-Plated Iron Construction with Aluminum Acrylic Coating Provides Durability, Impact Resistance and Corrosion Resistance.
Application	To Connect Conduit Sections
Standard	UL E2969, CSA
Hub Size	2 in
Material	Malleable Iron
Finish	Zinc Plating with Aluminum Acrylic Coating

Packaging

Outer Quantity	1
Outer Dimensions (inches)	12.87x10.75x4.37
Weight Uom	6.38 lbs. Each

Documents / Support Tools

Technical Drawing / Data Sheet	WSD-000258
--------------------------------	------------