



Actual

Catalog Number: TC103
Product ID: 7TAG009880R0002
UPC Number: 78621082244
EAN Number: 05414363057871
Status: A

Mounting Base, Natural Nylon 6.6 for Temperatures up to 85 Degrees Celsius (185 F), Length of 79mm (3.11 Inches), Width of 15.8mm (0.622 Inches), Height of 5.1mm (0.201 Inches), Screw Mounting Method, Bulk Pack

- These nylon bases provide a mounting range for bundles from 1/4 to 4 inches in diameter. One mounting hole is slotted to permit adjustment of the bundle position up to the time of actual bundle installation.

North American Specifications (UNSPSC)

| | |
|-----------------------|-----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| UNSPSC | 39121717 Cable tie mounts |
| IGCC | 5065 Cable tie mounts |
| Type | Mounting Base |
| Special Features | These nylon bases provide a mounting range for bundles from 1/4 to 4 inches in diameter. One mounting hole is slotted to permit adjustment of the bundle position up to the time of actual bundle installation. |
| Material | Nylon/Polyamide 6.6 |
| Color | Natural |
| Mounting | Screw |
| Operating Temperature | -40 to +185 F |

European Specifications (ETIM)

| | |
|---------------------------------|----------------------------------------------------|
| ETIM | EC000449 Mounting base and -element for cable ties |
| Length | 79mm |
| Width | 15.8mm |
| Height | 5.1mm |
| Suitable for cable tie width to | 7.6mm |
| For maximum bundle diameter | 1mm |
| Type of fastening | Other |
| Diameter mounting hole | 6.9mm |
| Material | Plastic |
| Material quality | Polyamide PA |
| Operating temperature | -40-+85°C |
| Colour | Natural colour |

Packaging

| | |
|---------------------------|----------------|
| Inner Quantity | 500 |
| Outer Quantity | 3000 |
| Outer Dimensions (inches) | 21.1x13.7x9.5 |
| Weight Uom | 1 lbs. per 100 |

Documents / Support Tools

| | |
|-----------------------------------|----------------------|
| Technical Drawing / Data Sheet US | Available on Website |
|-----------------------------------|----------------------|