



Actual

Catalog Number: TC106
Product ID: 7TAG009910R0071
UPC Number: 78621082250
EAN Number: 05414363057918
Status: A

Right-Angle Bundle Support, Natural Nylon 6.6 for Temperatures up to 85 Degrees Celsius (185 F), Length of 25.4mm (1.0 Inches), Width of 19.1mm (0.75 Inches), Height of 25.4mm (1.0 Inches), Two Screw Mounting Method, #4 Screw, Mounting Hole Size of 3.3mm (0.130 Inches)

- This style meets Military Specification requirements as a support at holes in bulkheads and walls.

North American Specifications (UNSPSC)

UNSPSC	39121717 Cable tie mounts
IGCC	5065 Cable tie mounts
Type	Right-Angle Bundle Support
Special Features	This style meets Military Specification requirements as a support at holes in bulkheads and walls.
Mount Size	#4
Material	Nylon/Polyamide 6.6
Color	Natural
Mounting	Screw
Operating Temperature	-40 to +185 F

European Specifications (ETIM)

ETIM	EC000449 Mounting base and -element for cable ties
Length	25.4mm
Width	19.1mm
Height	25.4mm
Suitable for cable tie width to	7.6mm
Type of fastening	Other
Diameter mounting hole	3.3mm
Material	Plastic
Material quality	Polyamide PA
Operating temperature	-40-+85°C
Colour	Natural colour

Packaging

Inner Quantity	200
Outer Quantity	1000
Outer Dimensions (inches)	16.3x8.4x7.6
Weight Uom	9.38 lbs. per 1000

Documents / Support Tools

Technical Drawing / Data Sheet US	Available on Website
-----------------------------------	----------------------