



Actual

Catalog Number: TC1104
Product ID: 7TAG009910R0075
UPC Number: 78621082643
EAN Number: 05414363057970
Status: A

Multiple Bundle Mounting Strip, Natural Nylon 6.6 for Temperatures up to 85 Degrees Celsius (185 F), Length of 139mm (5.5 Inches), Width of 12.7mm (0.50 Inch), Thickness of 3.17mm (0.125 Inch), Two-Screw Mounting Method, #6 Screw, Maximum Tie Width 4.82mm (0.19 Inch)

- These nylon mounting strips for parallel installation of wire bundles can accommodate up to six closely spaced bundles.

North American Specifications (UNSPSC)

UNSPSC	39121717 Cable tie mounts
IGCC	5065 Cable tie mounts
Type	Multiple Bundle Mounting Strip
Special Features	These nylon mounting strips for parallel installation of wire bundles can accommodate up to six closely spaced bundles.
Standard	UL E49405
Cable Size	0.19 in ; 4.82 mm
Material	Nylon/Polyamide 6.6
Color	Natural
Mounting	Screw
Operating Temperature	-40 to +185 F

European Specifications (ETIM)

ETIM	EC000449 Mounting base and -element for cable ties
Length	139mm
Width	12.7mm
Height	3.17mm
Suitable for cable tie width to	4.82mm
For maximum bundle diameter	4mm
Type of fastening	Other
Diameter mounting hole	3.71mm
Material	Plastic
Material quality	Polyamide PA
Operating temperature	-40-+85°C
Colour	Natural colour

Packaging

Inner Quantity	100
Outer Quantity	500
Outer Dimensions (inches)	9.75x8x6.5
Weight Uom	1.19 lbs. per 100

Documents / Support Tools

Technical Drawing / Data Sheet	WSD-000328
--------------------------------	------------