



Actual

Catalog Number: TC142-NDT
Product ID: 7TAG009660R0011
UPC Number: 78620902692
EAN Number: 05415022188318
Status: A

Saddle Support Mounting Base, Detectable Blue Nylon, Length of 23.4mm (0.92 Inch), Width of 14.2mm (0.56 Inch), Height of 10.67mm (0.42 Inch), Screw Mounting Method, #10 Pan Head Screw, Mounting Hole Size of 5.2mm (0.20 Inch), Bulk Pack

- Detectable with metal and X-ray detection equipment.
- This mounting base provides a saddle for the wire run. Ty-Rap tie is threaded under bundle and tied in a usual manner.

North American Specifications (UNSPSC)

UNSPSC	39121717 Cable tie mounts
IGCC	5065 Cable tie mounts
Type	Saddle Support Base
Special Features	Detectable with metal and X-ray detection equipment.
Material	Nylon/Polyamide 6.6
Color	Blue
Mounting	Screw
Operating Temperature	-40 to +185 F

European Specifications (ETIM)

ETIM	EC000449 Mounting base and -element for cable ties
Length	23.4mm
Width	14.2mm
Height	10.67mm
Suitable for cable tie width to	7.6mm
Type of fastening	Other
Material	Plastic with metal pigments
Material quality	Other
Operating temperature	-40-+85°C
Colour	Blue

Packaging

Inner Quantity	500
Inner Dimensions (inches)	15x12x3
Outer Quantity	5000
Outer Dimensions (inches)	18x12.9x13.6
Weight Uom	5 lbs. per 1000

Documents / Support Tools

Technical Drawing / Data Sheet	WSD-001086
--------------------------------	------------