



Actual

**Catalog Number:** TC342  
**Product ID:** 7TAG009820R0036  
**UPC Number:** 78621082312  
**EAN Number:** 05414363058465  
**Status:** A

Two-Way Mounting Base, Natural Nylon 6.6 for Temperatures up to 85 Degrees Celsius (185 F), Length of 28.6mm (1.13 Inches), Width of 28.6mm (1.13 Inches), Height of 5.7mm (0.22 Inches), Two-Component Glue Mounting Method, Bulk Pack

- One-piece molding - no lost parts. Consists of one tube each adhesive and activator.

#### North American Specifications (UNSPSC)

UNSPSC	39121717 Cable tie mounts
IGCC	5065 Cable tie mounts
Type	Mounting Base
Special Features	One-piece molding - no lost parts. Consists of one tube each adhesive and activator.
Material	Nylon/Polyamide 6.6
Color	Natural
Mounting	Epoxy Glue (TC2PA)
Operating Temperature	-40 to +185 F

#### European Specifications (ETIM)

ETIM	EC000449 Mounting base and -element for cable ties
Length	28.9mm
Width	28.9mm
Height	5.7mm
Suitable for cable tie width to	4.8mm
Type of fastening	Other
Material	Plastic
Material quality	Polyamide PA
Operating temperature	-40-+85°C
Colour	Natural colour

#### Packaging

Inner Quantity	1000
Inner Dimensions (inches)	20x14x0
Outer Quantity	5000
Outer Dimensions (inches)	21x13.3x10
Weight Uom	7.5 lbs. per 1000

#### Documents / Support Tools

Technical Drawing / Data Sheet US	Available on Website
-----------------------------------	----------------------