



Catalog Number: TC344A-NDT
Product ID: 7TAG009660R0013
UPC Number: 78620913084
EAN Number: 05415022188370
Status: A



Actual

Four-Way Adhesive Mounting Base, Blue Detectable Nylon 6.6 for Temperatures up to 65 Degrees Celsius (149 F), Length of 19mm (0.75 Inches), Width of 19mm (0.75 Inches), Height of 4.9mm (0.19 Inches), Self-Adhesive Mounting Method, Bulk Pack

- Detectable with metal and X-ray detection equipment.
- Eliminates errors in premounting the base with respect to its orientation to wire bundle direction.

North American Specifications (UNSPSC)

UNSPSC	39121717 Cable tie mounts
IGCC	5065 Cable tie mounts
Type	Mounting Base
Special Features	Detectable with metal and X-ray detection equipment.
Material	Nylon/Polyamide 6.6
Color	Blue
Mounting	Self-Adhesive
Operating Temperature	-32 to +150 F

European Specifications (ETIM)

ETIM	EC000449 Mounting base and -element for cable ties
Length	19.05mm
Width	19.05mm
Height	4.83mm
Suitable for cable tie width to	3.6mm
Type of fastening	Self-adhesive
Material	Plastic with metal pigments
Material quality	Other
Operating temperature	0-+65°C
Colour	Blue

Packaging

Inner Quantity	1000
Inner Dimensions (inches)	12x1x12
Outer Quantity	5000
Outer Dimensions (inches)	9.5x5x15.25
Weight Uom	0.16 lbs. per 100

Documents / Support Tools

Technical Drawing / Data Sheet	WSD-001087
Instruction Sheet	TA04709-TB2