



Catalog Number: TC347A-NDT
Product ID: 7TAG009660R0014
UPC Number: 78620913391
EAN Number: 05415022188400
Status: A



Actual

Four-Way and Two-Way Mounting Base With Open Leg Design, Detectable Blue Nylon 6.6 for Temperatures up to 65 Degrees Celsius (149 F), Length of 28.6mm (1.13 Inches), Width of 28.6mm (1.13 Inches), Height of 8.7mm (0.34 Inches), Self-Adhesive Mounting Method, Bulk Package

- Detectable with metal and X-ray detection equipment.
- Accommodates 4-way for ties up to .091 and 2-way for ties up to .301 maximum width.

North American Specifications (UNSPSC)

UNSPSC	39121717 Cable tie mounts
IGCC	5065 Cable tie mounts
Type	Mounting Base
Special Features	Detectable with metal and X-ray detection equipment.
Material	Nylon/Polyamide 6.6
Color	Blue
Mounting	Self-Adhesive
Operating Temperature	-32 to +150 F

European Specifications (ETIM)

ETIM	EC000449 Mounting base and -element for cable ties
Length	28.58mm
Width	28.58mm
Height	8.67mm
Suitable for cable tie width to	7.6mm
Type of fastening	Other
Diameter mounting hole	4.4mm
Material	Plastic with metal pigments
Material quality	Other
Operating temperature	0-+65°C
Colour	Blue

Packaging

Inner Quantity	1000
Inner Dimensions (inches)	20x1x14
Outer Quantity	5000
Outer Dimensions (inches)	13.12x9.12x20.75
Weight Uom	5 lbs. per 1000

Documents / Support Tools

Technical Drawing / Data Sheet	WSD-001087
Instruction Sheet	TA04709-TB2