



Actual

**Catalog Number:** TC350  
**Product ID:** 7TCG009900R0002  
**UPC Number:** 78621061451  
**EAN Number:** 05414363058670  
**Status:** A

Re-Usable Latching Cable Clamp, Natural Nylon 6.6 for Temperatures up to 85 Degrees Celsius (185 F), Length of 25.0mm (0.984 Inches), Width of 25.0mm (0.984 Inches), Maximum Height of 21.3mm (0.84 Inches), Screw Mounting Method, Mounting Hole Diameter of 4.3mm (0.17 Inches), Bulk Pack

#### North American Specifications (UNSPSC)

UNSPSC	39121702 Cable clips
IGCC	5029 Nylon Cable Clips
Type	Latching Clamp
Standard	UL E9809
Material	Nylon/Polyamide 6.6
Color	Natural
Mounting	Screw

#### European Specifications (ETIM)

ETIM	EC000449 Mounting base and -element for cable ties
Length	25mm
Width	25mm
Height	21.3mm
Type of fastening	Other
Diameter mounting hole	4.3mm
Material	Plastic
Material quality	Polyamide PA
Operating temperature	-40-+85°C
Colour	Natural colour

#### Packaging

Inner Quantity	1000
Outer Quantity	2000
Outer Dimensions (inches)	19.7x10.2x13.8
Weight Uom	8.24 lbs. per 1000