



Actual

**Catalog Number:** TC376  
**Product ID:** 7TAG009910R0086  
**UPC Number:** 78621082683  
**EAN Number:** 05414363058793  
**Status:** A

Stand-Off Brackets Mounting Base, Natural Nylon 6.6 for Temperatures up to 85 Degrees Celsius (185 F), Length of 44.45mm (1.75 Inches), Width of 17.5mm (0.69 Inches), Height of 17.0mm (0.67 Inches), Screw Mounting Method, Mounting Hole Diameter of 4.8mm (0.189 Inches)

- These brackets permit bundles to be mounted on either side. They also serve as means to raise bundles off the surface.

**North American Specifications (UNSPSC)**

UNSPSC	39121717 Cable tie mounts
IGCC	5065 Cable tie mounts
Type	Stand-Off Brackets
Special Features	These brackets permit bundles to be mounted on either side. They also serve as means to raise bundles off the surface.
Material	Nylon/Polyamide 6.6
Color	Natural
Mounting	Screw
Operating Temperature	-40 to +185 F

**European Specifications (ETIM)**

ETIM	EC000449 Mounting base and -element for cable ties
Length	44.45mm
Width	17.5mm
Height	17mm
Suitable for cable tie width to	5.8mm
Type of fastening	Other
Diameter mounting hole	4.8mm
Material	Plastic
Material quality	Polyamide PA
Operating temperature	-40-+85°C
Colour	Natural colour

**Packaging**

Inner Quantity	100
Outer Quantity	1000
Outer Dimensions (inches)	16.3x8.5x7.6
Weight Uom	5 lbs. per 1000

**Documents / Support Tools**

Technical Drawing / Data Sheet US	Available on Website
-----------------------------------	----------------------