



Actual

**Catalog Number:** TC402  
**Product ID:** 7TAG009900R0005  
**UPC Number:** 78620980302  
**EAN Number:** 05415022360981  
**Status:** A

Cable Edge Solar Clip U-Style for Managing Cable Parallel to the Frame, Black Acetal Copolymer for Outdoor Applications, Operating Temperature -65 to 90 Degrees Celsius (-85 to 194 F), Maximum Cable Diameter 7.87mm (0.31 Inch), Cable Capacity to to Four (4) #10 AWG Solar PV Control Cables

- Mount up to four #10 AWG Solar PV control cables cleanly and easily - keeping a professional look through panel rotation and vibration.
- Provides the ability to quickly slip the cables in and out of the clamp for ice removal, readjustment or other maintenance.
- Quick and easy installation, no tools required. Metal-free construction reduces the need for grounding.
- Material proven to perform over 20 years outdoor.
- Solar Panel projects.

### North American Specifications (UNSPSC)

UNSPSC	39121702 Cable clips
IGCC	5028 Cable clips
Type	Solar Clip
Special Features	Mount up to four #10 AWG Solar PV control cables cleanly and easily - keeping a professional look through panel rotation and vibration.
Application	Solar Panel projects.
Cable Size	#10 AWG
Cable Type	Solar PV Control
Number Of Cables	4
Material	Acetal
Color	Black
Mounting	Clip

### European Specifications (ETIM)

ETIM	EC000127 Saddle
Number of cables/conduits	4
Model	Half clamp
Type of fastening	Other
Material	Plastic
Material quality	Other
UV resistant	N

### Packaging

Inner Quantity	50
Inner Dimensions (inches)	12x12x4
Outer Quantity	500
Outer Dimensions (inches)	20.9x13.4x10
Weight Uom	4 lbs. per 100

### Documents / Support Tools

Marketing Brochure	Available on Website
--------------------	----------------------

