



Actual

Catalog Number: TC5141-NDT
Product ID: 7TAG009660R0017
UPC Number: 78620901923
EAN Number: 05415022188264
Status: A

Detectable Saddle Support Mounting Base, Detectable Blue Nylon, Length of 17.02mm (0.67 Inches), Width of 11.1mm (0.43 Inches), Screw Mounting Method, #6 Pan Head Screw, Mounting Hole Size of 3.8mm (0.15 Inches), 100 Pack

- Detectable with metal and X-ray detection equipment.
- This mounting base provides a saddle for the wire run. Ty-Rap tie is threaded under bundle and tied in a usual manner.

North American Specifications (UNSPSC)

UNSPSC	39121717 Cable tie mounts
IGCC	5065 Cable tie mounts
Type	Saddle Support Base
Special Features	Detectable with metal and X-ray detection equipment.
Material	Nylon/Polyamide 6.6
Color	Blue
Mounting	Screw
Operating Temperature	-40 to +185 F

European Specifications (ETIM)

ETIM	EC000449 Mounting base and -element for cable ties
Length	17.02mm
Width	11.1mm
Height	8.38mm
Suitable for cable tie width to	4.8mm
Type of fastening	Other
Diameter mounting hole	3.8mm
Material	Plastic with metal pigments
Material quality	Other
Operating temperature	-40-+85°C
Colour	Blue

Packaging

Inner Quantity	100
Inner Dimensions (inches)	8x4x1
Outer Quantity	500
Outer Dimensions (inches)	9.25x9.25x4.75
Weight Uom	1.25 lbs. per 1000

Documents / Support Tools

Technical Drawing / Data Sheet	WSD-001086
--------------------------------	------------