



Actual

Catalog Number: TC5342A-NDT
Product ID: 7TAG009660R0021
UPC Number: 78620905200
EAN Number: 05415022188325
Status: A

Two-Way Detectable Mounting Base, Detectable Blue Nylon 6.6 for Temperatures up to 65 Degrees Celsius (149 F), Length of 28.6mm (1.13 Inches), Width of 28.6mm (1.13 Inches), Height of 6.4mm (0.25 Inches), Self-Adhesive Mounting Method, 100 Pack

- Detectable with metal and X-ray detection equipment.
- One-piece molding - no lost parts

North American Specifications (UNSPSC)

UNSPSC	39121717 Cable tie mounts
IGCC	5065 Cable tie mounts
Type	Mounting Base
Special Features	Detectable with metal and X-ray detection equipment.
Material	Nylon/Polyamide 6.6
Color	Blue
Mounting	Self-Adhesive
Operating Temperature	-32 to +150 F

European Specifications (ETIM)

ETIM	EC000449 Mounting base and -element for cable ties
Length	28.58mm
Width	28.58mm
Height	6.35mm
Suitable for cable tie width to	4.8mm
Type of fastening	Self-adhesive
Material	Plastic with metal pigments
Material quality	Other
Operating temperature	0-+65°C
Colour	Blue

Packaging

Inner Quantity	100
Inner Dimensions (inches)	8x6x3
Outer Quantity	500
Outer Dimensions (inches)	9.5x6x7.75
Weight Uom	8.13 lbs. per 1000

Documents / Support Tools

Technical Drawing / Data Sheet	WSD-001087
Instruction Sheet	TA04709-TB2