



Actual

Catalog Number: TC5344A-NDT
Product ID: 7TAG009660R0023
UPC Number: 78620905866
EAN Number: 05415022188356
Status: A

Four-Way Adhesive Mounting Base, Detectable Blue Nylon 6.6 for Temperatures up to 65 Degrees Celsius (149 F), Length of 19mm (0.75 Inches), Width of 19mm (0.75 Inches), Height of 4.9mm (0.19 Inches), Self-Adhesive Mounting Method, 100 Pack

- Detectable with metal and X-ray detection equipment.
- Eliminates errors in premounting the base with respect to its orientation to wire bundle direction.

North American Specifications (UNSPSC)

UNSPSC	39121717 Cable tie mounts
IGCC	5065 Cable tie mounts
Type	Mounting Base
Special Features	Detectable with metal and X-ray detection equipment.
Material	Nylon/Polyamide 6.6
Color	Blue
Mounting	Self-Adhesive
Operating Temperature	-32 to +150 F

European Specifications (ETIM)

ETIM	EC000449 Mounting base and -element for cable ties
Length	19.05mm
Width	19.05mm
Height	4.83mm
Suitable for cable tie width to	3.6mm
Type of fastening	Other
Material	Plastic with metal pigments
Material quality	Other
Operating temperature	0-+65°C
Colour	Blue

Packaging

Inner Quantity	100
Inner Dimensions (inches)	12x1x6
Outer Quantity	500
Outer Dimensions (inches)	9.75x6.25x3.75
Weight Uom	1.25 lbs. per 1000

Documents / Support Tools

Technical Drawing / Data Sheet	WSD-001087
Catalog Page	Available on Website
Instruction Sheet	TA04709-TB2