



Representative

Catalog Number: TC5347AX
Product ID: 7TCG009800R0008
UPC Number: 78621054951
EAN Number: 05414363058991
Status: A

Four-Way and Two-Way Mounting Base With Open Leg Design, Black Nylon 6.6 for Temperatures up to 65 Degrees Celsius (149 F), Weather and UV Resistant, Length of 28.6mm (1.13 Inches), Width of 28.6mm (1.13 Inches), Height of 8.7mm (0.34 Inches), Self-Adhesive Mounting Method, 100 Pack

- Accommodates 4-way for ties up to .091 and 2-way for ties up to .301 maximum width.

North American Specifications (UNSPSC)

UNSPSC	39121717 Cable tie mounts
IGCC	5065 Cable tie mounts
Type	Mounting Base
Special Features	Accommodates 4-way for ties up to .091 and 2-way for ties up to .301 maximum width.
Material	Nylon/Polyamide 6.6 Weather Resistant
Color	Black
Mounting	Self-Adhesive
Operating Temperature	-32 to +150 F

European Specifications (ETIM)

ETIM	EC000449 Mounting base and -element for cable ties
Length	28.58mm
Width	28.58mm
Height	8.53mm
Suitable for cable tie width to	7.6mm
Type of fastening	Self-adhesive
Material	Plastic
Material quality	Polyamide PA
Operating temperature	0-+65°C
Colour	Black

Packaging

Inner Quantity	100
Outer Quantity	5000
Outer Dimensions (inches)	23.6x15.4x11
Weight Uom	5 lbs. per 1000

Documents / Support Tools

Technical Drawing / Data Sheet US	Available on Website
-----------------------------------	----------------------