



Actual

Catalog Number: TC5359
Product ID: 7TAG009850R0002
UPC Number: 78621080740
EAN Number: 05414363059103
Status: A

Heavy-Duty Wall Plug, Black Nylon 6.6 for Temperatures up to 85 Degrees Celsius, Weather and Ultraviolet Resistant, Length of 19.1mm (0.75 Inches), Width of 19.1mm (0.75 Inches), Height of 38.4mm (1.52 Inches), to be Used with Masonry and Brick Surfaces, Hole Size in Masonry of 9.5mm (0.375 Inches)

- Range-taking base to accommodate virtually all of cable-to-masonry clamping needs. Installs simply by tapping into a drilled hole.

North American Specifications (UNSPSC)

UNSPSC	39121717 Cable tie mounts
IGCC	5065 Cable tie mounts
Type	Heavy Duty Application
Special Features	Range-taking base to accommodate virtually all of cable-to-masonry clamping needs. Installs simply by tapping into a drilled hole.
Material	Nylon/Polyamide 6.6 Weather Resistant
Color	Black
Mounting	Push Mount
Operating Temperature	-40 to +185 F

European Specifications (ETIM)

ETIM	EC000449 Mounting base and -element for cable ties
Length	19.1mm
Width	19.1mm
Height	38.4mm
Suitable for cable tie width to	12.7mm
Type of fastening	Other
Diameter mounting hole	9.5mm
Material	Plastic
Material quality	Polyamide PA
Operating temperature	-40-+85°C
Colour	Black

Packaging

Inner Quantity	50
Outer Quantity	500
Outer Dimensions (inches)	17.25x12.75x6.5
Weight Uom	8.75 lbs. per 1000

Documents / Support Tools

Technical Drawing / Data Sheet US	Available on Website
-----------------------------------	----------------------