



Actual

Catalog Number: TCF050-27SS6
Product ID: 7TBD105310R0023
UPC Number: 78621092401
EAN Number: 05415022461619
Status: A

Tray/Cord Fitting, Hub Size NPT 1/2 Inch, Cable Diameter 0.150 to 0.270 Inch, Throat Diameter 0.330 Inch, 316 Stainless Steel

- Hand-tightens-no tools required
- Tapered neoprene bushing and O-ring seal out moisture and dirt ingress.
- Chuck grip provides high mechanical pull-out performance which exceeds applicable requirements.
- Silver Grip Tray/Cord fitting is the safe and cost effective choice for increased safety when terminating portable cord and try cable in hazardous locations.

North American Specifications (UNSPSC)

UNSPSC	39121431 Cable gland connector
IGCC	4601 Cable gland connector
Type	Tray/Cord Connectors
Special Features	Hand Tightens, No Tools Needed for Assembly
Application	Tray/Cord Fitting is The Safe and Cost Effective Choice for Increased Safety When Terminating Portable Cord and Try Cable In Hazardous Locations.
Standard	CSA
Size	1/2 Inch
Conductor Range	0.150 to 0.270 Inch
Material	Stainless Steel
Color	Metallic
Temperature Rating	90 C
Environmental Conditions	Gas and Vapour Environments

European Specifications (ETIM)

ETIM	EC001180 Screw connection for protective metallic hose
Nominal size in inch	1/2 inch
Model	Straight
Revolving thread	N
Construction type	External thread
Connection type screw connection to housing	Thread
One-piece	N
Material housing	Stainless steel
Surface protection	Untreated
Approved in combination with protective conduit CSA	Y

Packaging

Outer Quantity	25
Outer Dimensions (inches)	7.62x6.62x3.5
Weight Uom	18.38 lbs. per 100

Documents / Support Tools

Technical Drawing / Data Sheet US	Available on Website
-----------------------------------	----------------------

