



Catalog Number: TCF050-40AL
Product ID: 7TBD105320R0000
UPC Number: 78621087887
EAN Number: 05415022228472
Status: A



Actual



Representative

Tray/Cord Fitting, Hub Size NPT 1/2 Inch, Cable Diameter 0.250 to 0.400 Inch, Throat Diameter 0.540 Inch, Aluminum

- Hand-tightens-no tools required
- Tapered neoprene bushing and O-ring seal out moisture and dirt ingress.
- Corrosion-resistant, non-magnetic aluminum construction
- Chuck grip provides high mechanical pull-out performance which exceeds applicable requirements.
- Silver Grip™ Tray/Cord fitting is the safe and cost effective choice for increased safety when terminating portable cord and try cable in hazardous locations.

North American Specifications (UNSPSC)

UNSPSC	39121431 Cable gland connector
IGCC	4601 Cable gland connector
Type	Tray/Cord Connectors
Special Features	Hand Tightens, No Tools Needed for Assembly
Application	Tray/Cord Fitting is The Safe and Cost Effective Choice for Increased Safety When Terminating Portable Cord and Try Cable In Hazardous Locations.
Standard	CSA
Size	1/2 Inch
Conductor Range	0.250 to 0.400 Inch
Material	Aluminum
Color	Metallic
Temperature Rating	90 C
Environmental Conditions	Gas and Vapour Environments

European Specifications (ETIM)

ETIM	EC001180 Screw connection for protective metallic hose
Nominal size in inch	1/2 inch
Model	Straight
Revolving thread	N
Construction type	External thread
Connection type screw connection to housing	Thread
One-piece	N
Material housing	Other
Surface protection	Untreated
Approved in combination with protective conduit CSA	Y

Packaging

Outer Quantity	25
Outer Dimensions (inches)	8x7x4.25
Weight Uom	14.38 lbs. per 100

Documents / Support Tools

Technical Drawing / Data Sheet	TDS000045
Technical Drawing / Data Sheet US	Available on Website



Header

3D Model

Available on Website