



Actual

**Catalog Number:** TCF050-40SS6  
**Product ID:** 7TBD105310R0024  
**UPC Number:** 78621092407  
**EAN Number:** 05415022461626  
**Status:** A

Tray/Cord Fitting, Hub Size NPT 1/2 Inch, Cable Diameter 0.250 to 0.400 Inch, Throat Diameter 0.540 Inch, 316 Stainless Steel

- Hand-tightens-no tools required
- Tapered neoprene bushing and O-ring seal out moisture and dirt ingress.
- Chuck grip provides high mechanical pull-out performance which exceeds applicable requirements.
- Silver Grip Tray/Cord fitting is the safe and cost effective choice for increased safety when terminating portable cord and try cable in hazardous locations.

### North American Specifications (UNSPSC)

UNSPSC	39121431 Cable gland connector
IGCC	4601 Cable gland connector
Type	Tray/Cord Connectors
Special Features	Hand Tightens, No Tools Needed for Assembly
Application	Tray/Cord Fitting is The Safe and Cost Effective Choice for Increased Safety When Terminating Portable Cord and Try Cable In Hazardous Locations.
Standard	CSA
Size	1/2 Inch
Conductor Range	0.250 to 0.400 Inch
Material	Stainless Steel
Color	Metallic
Temperature Rating	90 C
Environmental Conditions	Gas and Vapour Environments

### European Specifications (ETIM)

ETIM	EC001180 Screw connection for protective metallic hose
Nominal size in inch	1/2 inch
Model	Straight
Revolving thread	N
Construction type	External thread
Connection type screw connection to housing	Thread
One-piece	N
Material housing	Stainless steel
Surface protection	Untreated
Approved in combination with protective conduit CSA	Y

### Packaging

Outer Quantity	25
Outer Dimensions (inches)	7.62x6.62x3.5
Weight Uom	40 lbs. per 100

### Documents / Support Tools

Technical Drawing / Data Sheet US	Available on Website
-----------------------------------	----------------------

