



Actual

Catalog Number: TCF050-67SS6
Product ID: 7TBD105980R0054
UPC Number: 78621094742
EAN Number: 05415022461510
Status: A

Tray/Cord Fitting, Hub Size NPT 1/2 Inch, Cable Diameter 0.540 to 0.670 Inch, Throat Diameter 0.540 Inch, 316 Stainless Steel

North American Specifications (UNSPSC)

UNSPSC	39121431 Cable gland connector
IGCC	4601 Cable gland connector
Type	Tray/Cord Connectors
Special Features	Hand Tightens, No Tools Needed for Assembly
Application	Tray/Cord Fitting is The Safe and Cost Effective Choice for Increased Safety When Terminating Portable Cord and Try Cable In Hazardous Locations.
Standard	CSA
Size	1/2 Inch
Conductor Range	0.540 to 0.670 Inch
Material	Stainless Steel
Color	Metallic
Temperature Rating	90 C
Environmental Conditions	Gas and Vapour Environments

European Specifications (ETIM)

ETIM	EC001180 Screw connection for protective metallic hose
Nominal size in inch	1/2 inch
Model	Straight
Revolving thread	N
Construction type	External thread
Connection type screw connection to housing	Thread
One-piece	N
Material housing	Stainless steel
Surface protection	Untreated
Approved in combination with protective conduit CSA	Y

Packaging

Outer Quantity	10
Outer Dimensions (inches)	8.68x4.37x3.5
Weight Uom	59 lbs. per 100

Documents / Support Tools

Technical Drawing / Data Sheet US	Available on Website
-----------------------------------	----------------------