



Actual



Representative

Project: Golden South
Location: Assiniboia, SK

Borea

Catalog Number: TCF100-100AL
Product ID: 7TBD105310R0035
UPC Number: 78621087958
EAN Number: 05415022460506
Status: A

Tray/Cord Fitting, Hub Size NPT 1 Inch, Cable Diameter 0.870 to 1.000 Inch, Throat Diameter 0.980 Inch, Aluminum

- Hand-tightens-no tools required
- Tapered neoprene bushing and O-ring seal out moisture and dirt ingress.
- Corrosion-resistant, non-magnetic aluminum construction
- Chuck grip provides high mechanical pull-out performance which exceeds applicable requirements.
- Silver Grip™ Tray/Cord fitting is the safe and cost effective choice for increased safety when terminating portable cord and try cable in hazardous locations.

North American Specifications (UNSPSC)

UNSPSC	39121431 Cable gland connector
IGCC	4601 Cable gland connector
Type	Tray/Cord Connectors
Special Features	Hand Tightens, No Tools Needed for Assembly
Application	Tray/Cord Fitting is The Safe and Cost Effective Choice for Increased Safety When Terminating Portable Cord and Try Cable In Hazardous Locations.
Standard	CSA
Size	1 Inch
Conductor Range	0.870 to 1.000 Inch
Material	Aluminum
Color	Metallic
Temperature Rating	90 C
Environmental Conditions	Gas and Vapour Environments

European Specifications (ETIM)

ETIM	EC001180 Screw connection for protective metallic hose
Nominal size in inch	1 inch
Model	Straight
Revolving thread	N
Construction type	External thread
Connection type screw connection to housing	Thread
One-piece	N
Material housing	Other
Surface protection	Untreated
Approved in combination with protective conduit CSA	Y

Packaging



Outer Quantity	10
Outer Dimensions (inches)	8.25x6.75x4.25
Weight Uom	37.5 lbs. per 100

Documents / Support Tools

Technical Drawing / Data Sheet	TDS000045
Technical Drawing / Data Sheet US	Available on Website

Header

3D Model	Available on Website
----------	----------------------