



Actual

Catalog Number: TCF100-88SS6
Product ID: 7TBD105310R0040
UPC Number: 78621094892
EAN Number: 05415022461824
Status: A

Tray/Cord Fitting, Hub Size NPT 1 Inch, Cable Diameter 0.770 to 0.880 Inch, Throat Diameter 0.980 Inch, 316 Stainless Steel

North American Specifications (UNSPSC)

UNSPSC	39121431 Cable gland connector
IGCC	4601 Cable gland connector
Type	Tray/Cord Connectors
Special Features	Hand Tightens, No Tools Needed for Assembly
Application	Tray/Cord Fitting is The Safe and Cost Effective Choice for Increased Safety When Terminating Portable Cord and Try Cable In Hazardous Locations.
Standard	CSA
Size	1 Inch
Conductor Range	0.770 to 0.880 Inch
Material	Stainless Steel
Color	Metallic
Temperature Rating	90 C
Environmental Conditions	Gas and Vapour Environments

European Specifications (ETIM)

ETIM	EC001180 Screw connection for protective metallic hose
Nominal size in inch	1 inch
Model	Straight
Revolving thread	N
Construction type	External thread
Connection type screw connection to housing	Thread
One-piece	N
Material housing	Stainless steel
Surface protection	Untreated
Approved in combination with protective conduit CSA	Y

Packaging

Outer Quantity	10
Outer Dimensions (inches)	7.62x6.62x3.5
Weight Uom	97.06 lbs. per 100

Documents / Support Tools

Technical Drawing / Data Sheet US	Available on Website
-----------------------------------	----------------------