



Actual



Representative

Catalog Number: TCF125-128AL
Product ID: 7TBD105310R0042
UPC Number: 78621093851
EAN Number: 05415022460742
Status: A

Tray/Cord Fitting, Hub Size NPT 1-1/4 Inch, Cable Diameter 1.080 to 1.280 Inch, Throat Diameter 1.255 Inch, Aluminum

- Hand-tightens-no tools required
- Tapered neoprene bushing and O-ring seal out moisture and dirt ingress.
- Corrosion-resistant, non-magnetic aluminum construction
- Chuck grip provides high mechanical pull-out performance which exceeds applicable requirements.
- Silver Grip™ Tray/Cord fitting is the safe and cost effective choice for increased safety when terminating portable cord and try cable in hazardous locations.

North American Specifications (UNSPSC)

UNSPSC	39121431 Cable gland connector
IGCC	4601 Cable gland connector
Type	Tray/Cord Connectors
Special Features	Hand Tightens, No Tools Needed for Assembly
Application	Tray/Cord Fitting is The Safe and Cost Effective Choice for Increased Safety When Terminating Portable Cord and Try Cable In Hazardous Locations.
Standard	CSA
Size	1-1/4 Inch
Conductor Range	1.080 to 1.280 Inch
Material	Aluminum
Color	Metallic
Temperature Rating	90 C
Environmental Conditions	Gas and Vapour Environments

European Specifications (ETIM)

ETIM	EC001180 Screw connection for protective metallic hose
Nominal size in inch	1 1/4 inch
Model	Straight
Revolving thread	N
Construction type	External thread
Connection type screw connection to housing	Thread
One-piece	N
Material housing	Other
Surface protection	Untreated
Approved in combination with protective conduit CSA	Y

Packaging

Outer Quantity	4
Outer Dimensions (inches)	9.75x6.25x3.5
Weight Uom	60 lbs. per 100

Documents / Support Tools

Technical Drawing / Data Sheet	TDS000045
Technical Drawing / Data Sheet US	Available on Website



Header

3D Model

Available on Website