



Actual

Catalog Number: TS2045HF
Product ID: 7TCG054360R0064
UPC Number: 78621059822
EAN Number: 05414363059936
Status: A

Flame Retardant Cable Tie, Natural Polyamide (Nylon 6.6) for Temperatures up to 85 Degrees Celsius (185 F), Length 200mm (7.87 Inches), Width 4.5mm (0.177 Inches), Tensile Strength Rating of 220 Newtons (50 Pounds)

North American Specifications (UNSPSC)

UNSPSC	39121703 Cable ties
IGCC	5034 Cable ties
Type	Flame Retardant
Width	0.177 in ; 4.5 mm
Length	7.87 in ; 200 mm
Bundle Diameter	2 in ; 50.8 mm
Material	Nylon/Polyamide 6.6
Color	Natural
Lock Mechanism	Plastic Pawl
Tensile Strength	50 pounds ; 222 newtons

European Specifications (ETIM)

ETIM	EC000046 Cable tie
Band width	4.5mm
Length belt/tape/tie	200mm
Max. bundle diameter	51mm
Min. holding force	220N
Operating temperature	-40-+85°C
Model	Internal toothing
Band closure	Plastic lip/-cam
Material	Plastic
Material quality	Polyamide PA
Surface protection	Untreated
Halogen free	Y
Colour	Natural colour
Transparent	N
Reflective (fluorescent)	N
Text strip	None
Solvable fastener	N
MIL approval	N
UL approval	N

Packaging

Inner Quantity	100
Outer Quantity	10000
Weight Uom	0.3 lbs. per 100