



Actual

Catalog Number: TY-TOTE-28
Product ID: 7TAG009930R0014
UPC Number: 78621097941
EAN Number: 05415022189650
Status: A

Polyester Cable Tie Dispenser for 279.4mm (11 Inch) and 355.6mm (14 Inch) Ties, Includes 1 Package of Cable Ties -Cable Tie, Natural Polyamide (Nylon 6.6) for Temperatures up to 85 Degrees Celsius (185 F) for Indoor Applications, UL/EN/CSA62275 Type 2/21S Rated for AH-2 Plenum or as a Flexible Cable and Conduit Support, Length of 360.5mm (14.2 Inches), Width of 4.82mm (0.19 Inches), Thickness of 1.4mm (0.05 Inches), Tensile Strength Rating of 222 Newtons (50 Pounds)

- Attach to your belt or almost any other convenient location via a built-in belt clip and chrome steel loop.
- Easily remove the tie you need through the reinforced, diamond-shaped cut while the Ty-Rap Tote securely holds the rest.

North American Specifications (UNSPSC)

UNSPSC	39121703 Cable ties
IGCC	5034 Cable ties
Type	Cable Tie Dispenser
Special Features	Attach to your belt or almost any other convenient location via a built-in belt clip and chrome steel loop.
Material	Polyester
Color	Blue

European Specifications (ETIM)

ETIM	EC002225 Tool belt
Material	Plastic

Packaging

Inner Quantity	1
Inner Dimensions (inches)	6x18x4
Outer Quantity	10
Outer Dimensions (inches)	22x9x7.75
Weight Uom	93.75 lbs. per 100

Documents / Support Tools

Technical Drawing / Data Sheet	Available on Website
--------------------------------	----------------------