



Representative

Catalog Number: TY1X4WHW6
Product ID: 7TAA104070R0005
UPC Number: 78620988467
Status: A

Wiring Duct Halogen Free Wide Slot 1 Inch X 4 Inch Modified PPE White

- Higher temperature rating than PVC.
- Wide fingers and slots increase rigidity and enable insertion of bundles.
- V-Shaped slot lead-in enables easier and faster wire installation.
- Rounded edges keep hands and wires free of abrasion.
- Non-slip cover does not slide easily and resists vibration.
- Flush cover attaches flush with sidewall for finished look.
- Dual score lines are designed to yield clean breakoffs at the base of the slot and the duct.
- Versatile North American and DIN Standard mounding holes enables same duct for multiple applications.

North American Specifications (UNSPSC)

UNSPSC	39131712 Wiring duct
IGCC	5580 Wiring duct
Type	Wide Slot Duct
Special Features	Higher temperature rating than PVC. Wide fingers and slots increase rigidity and enable insertion of bundles. V-Shaped slot lead-in enables easier and faster wire installation. Rounded edges keep hands and wires free of abrasion.
Width	1.25 in ; 31.75 mm
Depth	4.37 in ; 111 mm
Length	6 in ; 152.4 mm
Mounting Holes	Yes
Material	Modified PPE
Color	White

European Specifications (ETIM)

ETIM	EC000012 Slotted cable trunking system
Height	111mm
Width	31.8mm
Type of side wall	Slotted
Length	1829mm
Halogen free	Y
Flexible	N
Type of fastening	Adhesive film
With cover	N
Colour	White

Packaging

Inner Quantity	6
Inner Dimensions (inches)	72x1x4
Outer Quantity	60
Outer Dimensions (inches)	72x9.5x7
Weight Uom	45 lbs. per 100

Documents / Support Tools

Technical Drawing / Data Sheet	WSD-000283
--------------------------------	------------

Catalog Page

Available on Website