

Catalog Number: TY232M-1
Product ID: 7TAG009070R0083
UPC Number: 78621063360
EAN Number: 05414363061434
Status: A



Actual

Cable Tie, Brown Polyamide (Nylon 6.6) for Temperatures up to 85 Degrees Celsius (185 F) for Indoor Applications, UL/EN/CSA62275 Type 2/21 Rated for AH-2 Plenum, Length of 203.2mm (8.0 Inches), Width of 2.54mm (0.10 Inches), Thickness of 1.10mm (0.043 Inches), Tensile Strength Rating of 80 Newtons (18 Pounds), Bulk Pack

North American Specifications (UNSPSC)

UNSPSC	39121703 Cable ties
IGCC	5034 Cable ties
Type	High Performance
Standard	UL E49405
Width	0.1 in ; 2.54 mm
Length	8 in ; 203.2 mm
Thickness	0.043 in ; 1.1 mm
Material	Nylon/Polyamide 6.6
Color	Brown
Lock Mechanism	Stainless Steel Barb
Tensile Strength	18 pounds ; 80 newtons

European Specifications (ETIM)

ETIM	EC000046 Cable tie
Band width	2.54mm
Length belt/tape/tie	203.2mm
Tie thickness	1.1mm
Max. bundle diameter	50mm
Min. holding force	80N
Operating temperature	-40-+85°C
Model	Internal toothing
Band closure	Steel nose
Material	Plastic
Material quality	Polyamide PA
Surface protection	Untreated
UV-stable acc. ASTM D6779	N
Halogen free	Y
Colour	Brown
Transparent	N
Reflective (fluorescent)	N
Text strip	None
Solvable fastener	N
VG approval	N
MIL approval	N
UL approval	Y

Packaging

Inner Quantity	1000
Inner Dimensions (inches)	15x12x2
Outer Quantity	10000
Outer Dimensions (inches)	13.5x11.2x10.9
Weight Uom	0.63 lbs. per 1000

Documents / Support Tools

Technical Drawing / Data Sheet US	Available on Website
-----------------------------------	----------------------

