



Actual

**Catalog Number:** TY242M-3  
**Product ID:** 7TAG009160R0006  
**UPC Number:** 78621063647  
**EAN Number:** 05414363061915  
**Status:** A

Cable Tie, Orange Polyamide (Nylon 6.6) for Temperatures up to 85 Degrees Celsius (185 F) for Indoor Applications, UL/EN/CSA62275 Type 2/21 Rated for AH-2 Plenum, Length of 208mm (8.2 Inches), Width of 3.6mm (0.14 Inches), Thickness of 1mm (0.04 Inch), Tensile Strength Rating of 178 Newtons (40 Pounds), Bulk Pack

**North American Specifications (UNSPSC)**

UNSPSC	39121703 Cable ties
IGCC	5034 Cable ties
Type	High Performance
Standard	UL E49405
Width	0.14 in ; 3.6 mm
Length	8.2 in ; 208 mm
Thickness	0.04 in ; 1.0 mm
Bundle Diameter	0.08 to 2.01 in ; 2 to 51 mm
Material	Nylon/Polyamide 6.6
Color	Orange
Lock Mechanism	Stainless Steel Barb
Tensile Strength	40 pounds ; 178 newtons

**European Specifications (ETIM)**

ETIM	EC000046 Cable tie
Band width	3.6mm
Length belt/tape/tie	208mm
Tie thickness	1.0mm
Max. bundle diameter	51mm
Min. holding force	178N
Operating temperature	-40-+85°C
Model	Internal toothing
Band closure	Steel nose
Material	Plastic
Material quality	Polyamide PA
Surface protection	Untreated
UV-stable acc. ASTM D6779	N
Halogen free	Y
Colour	Orange
Transparent	N
Reflective (fluorescent)	N
Text strip	None
Solvable fastener	N
VG approval	N
MIL approval	N
UL approval	Y

**Packaging**

Inner Quantity	1000
Inner Dimensions (inches)	18x12x2
Outer Quantity	10000
Outer Dimensions (inches)	20.9x9.7x13.2
Weight Uom	1.88 lbs. per 1000

**Documents / Support Tools**

Technical Drawing / Data Sheet	TDS000566
--------------------------------	-----------

