



Actual

**Catalog Number:** TY253M-1  
**Product ID:** 7TAG009270R0002  
**UPC Number:** 78621015136  
**EAN Number:** 05414363062318  
**Status:** Active

Cable Tie, Brown Polyamide (Nylon 6.6) for Temperatures up to 85 Degrees Celsius (185 F) for Indoor Applications, UL/EN/CSA62275 Type 2/21S Rated for AH-2 Plenum and as a Flexible Cable and Conduit Support, Length of 289.7mm (11.40 Inches), Width of 4.82mm (0.19 Inches), Thickness of 1.41mm (0.055 Inches), Tensile Strength Rating of 222 Newtons (50 Pounds), Military Specified (MIL-SPEC MS3367-7-1), Bulk Pack

### North American Specifications (UNSPSC)

UNSPSC	39121703 Cable ties
IGCC	5037 Cable Ties & Wraps
Brand Name	Ty-Rap
Standard	UL E49405
Width	0.189 in ; 4.82 mm
Length	11.4 in ; 289.7 mm
Thickness	0.055 Inch/1.41mm
Material	Nylon/Polyamide 6.6
Color	Brown
Lock Mechanism	Stainless Steel Barb
Tensile Strength	50 Pounds/220 Newtons

### European Specifications (ETIM)

ETIM	EC000046 Cable tie
Band width	4.82mm
Length belt/tape/tie	289.7mm
Tie thickness	1.41mm
Max. bundle diameter	78mm
Min. holding force	222N
Operating temperature	-40-+85°C
Model	Internal toothing
Band closure	Steel nose
Material	Plastic
Material quality	Polyamide PA
Surface protection	Untreated
UV-stable acc. ASTM D6779	N
Halogen free	Y
Colour	Brown
Transparent	N
Reflective (fluorescent)	N
Text strip	None
Solvable fastener	N
VG approval	N
MIL approval	Y
UL approval	Y

### Packaging

Inner Quantity	1000
Outer Quantity	5000
Outer Dimensions (inches)	14x13x12.5
Weight Uom	0.44 lbs. per 100

### Documents / Support Tools

Technical Drawing / Data Sheet US	Available on Website
Technical Drawing / Data Sheet Canada	Available on Website

Thomas & Betts - USA