



Actual

**Catalog Number:** TY253M-3  
**Product ID:** 7TAG009270R0004  
**UPC Number:** 78621090325  
**EAN Number:** 05414363062349  
**Status:** A

High Performance Cable Tie for Indoor applications, Orange Color Nylon 6.6, Length of 295mm (11.6 Inches) for Bundle Diameter up to 78mm (3 Inches), Width of 4.67mm (0.184 Inch), Tensile Strength Rating of 220 Newtons (50 Pounds), Operating Temperature of -60 Degrees Celsius (-76 F) to 85 Degrees Celsius (185 F), UL/EN/CSA62275 Type 2/21S Rated for AH-2 Plenum and as a Flexible Cable and Conduit Support, Military Specified (MIL-SPEC MS3367-7-3), Bulk Pack

**North American Specifications (UNSPSC)**

UNSPSC	39121703 Cable ties
IGCC	5034 Cable ties
Type	High Performance
Standard	UL E49405
Width	0.189 in ; 4.82 mm
Length	11.4 in ; 289.7 mm
Thickness	0.055 in ; 1.4 mm
Material	Nylon/Polyamide 6.6
Color	Orange
Lock Mechanism	Stainless Steel Barb
Tensile Strength	50 pounds ; 220 newtons

**European Specifications (ETIM)**

ETIM	EC000046 Cable tie
Band width	4.82mm
Length belt/tape/tie	289.7mm
Tie thickness	1.41mm
Max. bundle diameter	78mm
Min. holding force	222N
Operating temperature	-40-+85°C
Model	Internal tothing
Band closure	Steel nose
Material	Plastic
Material quality	Polyamide PA
Surface protection	Untreated
UV-stable acc. ASTM D6779	N
Halogen free	Y
Colour	Orange
Transparent	N
Reflective (fluorescent)	N
Text strip	None
Solvable fastener	N
VG approval	N
MIL approval	Y
UL approval	Y

**Packaging**

Inner Quantity	1000
Outer Quantity	5000
Outer Dimensions (inches)	14x13x12.5
Weight Uom	0.63 lbs. per 1000

**Documents / Support Tools**

Technical Drawing / Data Sheet	WSD-003269
--------------------------------	------------

