



Catalog Number: TY253M-8
Product ID: 7TAG009270R0008
UPC Number: 78621074125
EAN Number: 05414363062394
Status: A



Actual

High Performance Cable Tie for Indoor applications, Gray Color Nylon 6.6, Length of 295mm (11.6 Inches) for Bundle Diameter up to 78mm (3 Inches), Width of 4.67mm (0.184 Inch), Tensile Strength Rating of 220 Newtons (50 Pounds), Operating Temperature of -60 Degrees Celsius (-76 F) to 85 Degrees Celsius (185 F), UL/EN/CSA62275 Type 2/21S Rated for AH-2 Plenum and as a Flexible Cable and Conduit Support, Military Specified (MIL-SPEC MS3367-7-8), Bulk Pack

North American Specifications (UNSPSC)

UNSPSC	39121703 Cable ties
IGCC	5034 Cable ties
Type	High Performance
Standard	UL E49405
Width	0.189 in ; 4.82 mm
Length	11.4 in ; 289.7 mm
Thickness	0.055 in ; 1.4 mm
Material	Nylon/Polyamide 6.6
Color	Gray
Lock Mechanism	Stainless Steel Barb
Tensile Strength	50 pounds ; 220 newtons

European Specifications (ETIM)

ETIM	EC000046 Cable tie
Band width	4.82mm
Length belt/tape/tie	289.7mm
Tie thickness	1.41mm
Max. bundle diameter	78mm
Min. holding force	222N
Operating temperature	-40-+85°C
Model	Internal toothing
Band closure	Steel nose
Material	Plastic
Material quality	Polyamide PA
Surface protection	Untreated
UV-stable acc. ASTM D6779	N
Halogen free	Y
Colour	Grey
Transparent	N
Reflective (fluorescent)	N
Text strip	None
Solvable fastener	N
VG approval	N
MIL approval	Y
UL approval	Y

Packaging

Inner Quantity	1000
Inner Dimensions (inches)	.2x14x.01
Outer Quantity	5000
Outer Dimensions (inches)	19.75x11.5x9.38
Weight Uom	6.88 lbs. per 1000

Documents / Support Tools

