



Actual

Catalog Number: TY26M-3
Product ID: 7TAG009160R0026
UPC Number: 78621084495
EAN Number: 05414363062813
Status: A

Cable Tie, Orange Polyamide (Nylon 6.6) for Temperatures up to 85 Degrees Celsius (185 F) for Indoor Applications, UL/EN/CSA62275 Type 2/21 Rated for AH-2 Plenum, Length of 277mm (10.9 Inches), Width of 3.6mm (0.14 Inch), Thickness of 1mm (0.04 Inch), Tensile Strength Rating of 134 Newtons (30 Pounds), Bulk Pack

- Low profile head is designed to prevent snags on uneven surfaces and easier to pull through bulkheads. Non-magnetic stainless steel locking device insures both maximum strength and the right tightness every time.
- Because there are no notches, Ty-Rap ties provide an infinite number of locking positions while fastening the tie at the precise bundle diameter needed.
- The No-Slip Tail provides easy grip during tensioning. Ty-Rap ties feature a unique friction surface designed to reduce slippage during installation.
- Smooth, notchless body reduces stress concentration points under tension, making the tie stronger and lower profile than notched body ties. Ribbed and Stippled body grips the bundle and prevents slippage. Rounded edges protect insulation, preventing sharp edges from damaging cables.
- Application Tools: WT199, ERG50, WT1-TB

North American Specifications (UNSPSC)

UNSPSC	39121703 Cable ties
IGCC	5034 Cable ties
Type	High Performance
Special Features	Low profile head is designed to prevent snags on uneven surfaces and easier to pull through bulkheads. Non-magnetic stainless steel locking device insures both maximum strength and the right tightness every time.
Standard	UL E49405
Width	0.14 in ; 3.6 mm
Length	10.9 in ; 277 mm
Thickness	0.04 in ; 1.0 mm
Bundle Diameter	0.08 to 2.99 in ; 2 to 76 mm
Material	Nylon/Polyamide 6.6
Color	Orange
Tensile Strength	30 pounds ; 134 newtons

European Specifications (ETIM)

ETIM	EC000046 Cable tie
Band width	3.6mm
Length belt/tape/tie	277mm
Tie thickness	1.0mm
Max. bundle diameter	76mm
Min. holding force	134N
Operating temperature	-40-+85°C
Model	Internal toothing
Band closure	Steel nose
Material	Plastic
Material quality	Polyamide PA
Surface protection	Untreated
UV-stable acc. ASTM D6779	N
Halogen free	Y



Colour	Orange
Transparent	N
Reflective (fluorescent)	N
Text strip	None
Solvable fastener	N
VG approval	N
MIL approval	N
UL approval	Y

Packaging

Inner Quantity	1000
Inner Dimensions (inches)	16x12x0
Outer Quantity	10000
Outer Dimensions (inches)	21.6x9.6x14
Weight Uom	2.5 lbs. per 1000

Documents / Support Tools

Technical Drawing / Data Sheet	TDS000566
--------------------------------	-----------