



Actual

Catalog Number: TY272M-5
Product ID: 7TAG009370R0005
UPC Number: 78621081755
EAN Number: 05414363063025
Status: A

Cable Tie, Green Polyamide (Nylon 6.6) for Temperatures up to 85 Degrees Celsius (185 F) for Indoor Applications, UL/EN/CSA62275 Type 2/21S Rated for AH-2 Plenum and as a Flexible Cable and Conduit Support, Length of 222.3mm (8.75 Inches), Width of 6.99mm (0.275 Inches), Thickness of 1.78mm (0.07 Inches), Tensile Strength Rating of 534 Newtons (120 Pounds), Bulk Pack

North American Specifications (UNSPSC)

UNSPSC	39121703 Cable ties
IGCC	5034 Cable ties
Type	High Performance
Standard	UL E49405
Width	0.275 in ; 6.99 mm
Length	8.75 in ; 222.3 mm
Thickness	0.07 in ; 1.78 mm
Material	Nylon/Polyamide 6.6
Color	Green
Lock Mechanism	Stainless Steel Barb
Tensile Strength	120 pounds ; 540 newtons

European Specifications (ETIM)

ETIM	EC000046 Cable tie
Band width	6.99mm
Length belt/tape/tie	222.3mm
Tie thickness	1.78mm
Max. bundle diameter	50mm
Min. holding force	534N
Operating temperature	-40-+85°C
Model	Internal toothing
Band closure	Steel nose
Material	Plastic
Material quality	Polyamide PA
Surface protection	Untreated
UV-stable acc. ASTM D6779	N
Halogen free	Y
Colour	Green
Transparent	N
Reflective (fluorescent)	N
Text strip	None
Solvable fastener	N
VG approval	N
MIL approval	N
UL approval	Y

Packaging

Inner Quantity	500
Inner Dimensions (inches)	11.5x3.6x8.8
Outer Quantity	1000
Outer Dimensions (inches)	15.3x9.5x5
Weight Uom	6.88 lbs. per 1000

