



Actual

**Catalog Number:** TY275M2  
**Product ID:** 7TAG009370R0014  
**UPC Number:** 78621084650  
**EAN Number:** 05414363063117  
**Status:** A

High Performance Cable Tie for Indoor Applications, Red Color Nylon 6.6, Length of 457mm (18 Inches) for Bundle Diameter up to 127mm (5 Inches), Width of 6.9mm (0.271 Inch), Tensile Strength Rating of 534 Newtons (120 Pounds), Operating Temperature of -60 Degrees Celsius (-76 F) to 85 Degrees Celsius (185 F), UL/EN/CSA62275 Type 2/21S Rated for AH-2 Plenum and as a Flexible Cable and Conduit Support, Bulk Pack

### North American Specifications (UNSPSC)

UNSPSC	39121703 Cable ties
IGCC	5034 Cable ties
Type	High Performance
Standard	UL E49405
Width	0.27 in ; 7 mm
Length	18 in ; 457 mm
Thickness	0.06 in ; 1.65 mm
Material	Nylon/Polyamide 6.6
Color	Red
Lock Mechanism	Stainless Steel Barb
Tensile Strength	120 pounds ; 540 newtons

### European Specifications (ETIM)

ETIM	EC000046 Cable tie
Band width	7mm
Length belt/tape/tie	457mm
Tie thickness	1.65mm
Max. bundle diameter	127mm
Min. holding force	530N
Operating temperature	-40-+85°C
Model	Internal toothing
Band closure	Steel nose
Material	Plastic
Material quality	Polyamide PA
Surface protection	Untreated
UV-stable acc. ASTM D6779	N
Halogen free	Y
Colour	Red
Transparent	N
Reflective (fluorescent)	N
Text strip	None
Solvable fastener	N
VG approval	N
MIL approval	N
UL approval	Y

### Packaging

Outer Quantity	500
Outer Dimensions (inches)	9x4x22.5
Weight Uom	3.13 lbs. per 100

### Documents / Support Tools

Technical Drawing / Data Sheet US	Available on Website
Catalog Page	Available on Website

