

Catalog Number: TY275M3
Product ID: 7TAG009370R0015
UPC Number: 78621084653
EAN Number: 05414363063124
Status: A



Actual

High Performance Cable Tie for Indoor Applications, Orange Color Nylon 6.6, Length of 457mm (18 Inches) for Bundle Diameter up to 127mm (5 Inches), Width of 6.9mm (0.27 Inch), Tensile Strength Rating of 534 Newtons (120 Pounds), Operating Temperature of -60 Degrees Celsius (-76 F) to 85 Degrees Celsius (185 F), UL/EN/CSA62275 Type 2/21S Rated for AH-2 Plenum and as a Flexible Cable and Conduit Support, Bulk Pack

- Low profile head is designed to prevent snags on uneven surfaces and easier to pull through bulkheads. Non-magnetic stainless steel locking device insures both maximum strength and the right tightness every time.
- Because there are no notches, Ty-Rap ties provide an infinite number of locking positions while fastening the tie at the precise bundle diameter needed.
- The No-Slip Tail provides easy grip during tensioning. Ty-Rap ties feature a unique friction surface designed to reduce slippage during installation.
- Application Tools: ERG120, WT197

North American Specifications (UNSPSC)

UNSPSC	39121703 Cable ties
IGCC	5034 Cable ties
Type	High Performance
Special Features	Low profile head is designed to prevent snags on uneven surfaces and easier to pull through bulkheads. Non-magnetic stainless steel locking device insures both maximum strength and the right tightness every time.
Standard	UL E49405
Width	0.27 in ; 7 mm
Length	18 in ; 457 mm
Thickness	0.06 in ; 1.65 mm
Bundle Diameter	0.236 to 5 in ; 6 to 127 mm
Material	Nylon/Polyamide 6.6
Color	Orange
Lock Mechanism	Stainless Steel Barb
Tensile Strength	120 pounds ; 530 newtons

European Specifications (ETIM)

ETIM	EC000046 Cable tie
Band width	6.9mm
Length belt/tape/tie	457mm
Tie thickness	1.5mm
Max. bundle diameter	127mm
Min. holding force	540N
Operating temperature	-60-+85°C
Model	Internal toothing
Band closure	Steel nose
Material	Plastic
Material quality	Polyamide PA
Surface protection	Untreated
UV-stable acc. ASTM D6779	N
Halogen free	Y
Colour	Orange
Transparent	N



Reflective (fluorescent)	N
Text strip	None
Solvable fastener	N
VG approval	N
MIL approval	N
UL approval	Y

Packaging

Outer Quantity	500
Outer Dimensions (inches)	10x10x10
Weight Uom	1.19 lbs. per 100

Documents / Support Tools

Technical Drawing / Data Sheet	TDS000487
--------------------------------	-----------