



Actual

Catalog Number: TY277M-5
Product ID: 7TAG009370R0020
UPC Number: 78621076889
EAN Number: 05414363063223
Status: A

High Performance Cable Tie for Indoor Applications, Green Color Nylon 6.6, Length of 617mm (24.3 Inches) for Bundle Diameter up to 177mm (6.96 Inches), Width of 6.9mm (0.27 Inch), Tensile Strength Rating of 534 Newtons (120 Pounds), Operating Temperature of -60 Degrees Celsius (-76 F) to 85 Degrees Celsius (185 F), UL/EN/CSA62275 Type 2/21S Rated for AH-2 Plenum and as a Flexible Cable and Conduit Support, Bulk Pack

North American Specifications (UNSPSC)

UNSPSC	39121703 Cable ties
IGCC	5034 Cable ties
Type	High Performance
Standard	UL E49405
Width	0.27 in ; 7 mm
Length	24.3 in ; 617 mm
Thickness	0.06 in ; 1.65 mm
Material	Nylon/Polyamide 6.6
Color	Green
Lock Mechanism	Stainless Steel Barb
Tensile Strength	120 pounds ; 540 newtons

European Specifications (ETIM)

ETIM	EC000046 Cable tie
Band width	6.9mm
Length belt/tape/tie	617mm
Tie thickness	1.5mm
Max. bundle diameter	177mm
Min. holding force	540N
Operating temperature	-60-+85°C
Model	Internal toothing
Band closure	Steel nose
Material	Plastic
Material quality	Polyamide PA
Surface protection	Untreated
UV-stable acc. ASTM D6779	N
Halogen free	Y
Colour	Green
Transparent	N
Reflective (fluorescent)	N
Text strip	None
Solvable fastener	N
VG approval	N
MIL approval	N
UL approval	Y

Packaging

Outer Quantity	500
Outer Dimensions (inches)	28.8x11.5x5.9
Weight Uom	19.38 lbs. per 1000

Documents / Support Tools

Technical Drawing / Data Sheet	TDS000487
--------------------------------	-----------

