



Actual

**Catalog Number:** TY27M-7  
**Product ID:** 7TAG009370R0028  
**UPC Number:** 78621084505  
**EAN Number:** 05414363063339  
**Status:** A

High Performance Cable Tie, Purple Nylon 6.6, Length of 343mm (13.5 Inches) for Bundle Diameter up to 102mm (4 Inches), Width of 6.9mm (0.27 Inch), Tensile Strength Rating of 534 Newtons (120 Pounds), Operating Temperature of -20 Degrees Celsius (-4 F) to 85 Degrees Celsius (185 F)

- 316 stainless steel barb is corrosion resistant and provides greater longevity

#### North American Specifications (UNSPSC)

UNSPSC	39121703 Cable ties
IGCC	5034 Cable ties
Type	High Performance
Standard	UL E49405
Width	0.27 in ; 6.9 mm
Length	13.5 in ; 343 mm
Thickness	0.06 in ; 1.5 mm
Bundle Diameter	Max 4.02 in ; Max 102 mm
Material	Nylon/Polyamide 6.6
Color	Purple
Lock Mechanism	Stainless Steel Barb
Tensile Strength	120 pounds ; 534 newtons

#### European Specifications (ETIM)

ETIM	EC000046 Cable tie
Band width	7mm
Length belt/tape/tie	343mm
Tie thickness	1.65mm
Max. bundle diameter	90mm
Min. holding force	530N
Operating temperature	-60-+85°C
Model	Internal toothing
Band closure	Steel nose
Material	Plastic
Material quality	Polyamide PA
Surface protection	Untreated
UV-stable acc. ASTM D6779	N
Halogen free	Y
Colour	Purple/violet
Transparent	N
Reflective (fluorescent)	N
Text strip	None
Solvable fastener	N
VG approval	N
MIL approval	Y
UL approval	Y

#### Packaging

Inner Quantity	500
Outer Quantity	1000
Outer Dimensions (inches)	22x14x0
Weight Uom	3.75 lbs. per 1000

#### Documents / Support Tools



Technical Drawing / Data Sheet

TDS000487