



**Catalog Number:** TY27M-NDT  
**Product ID:** 7TAG009660R0028  
**UPC Number:** 78620993668  
**EAN Number:** 05415022262148  
**Status:** A



Actual

Detectable Cable Tie, Bright Blue Polyamide (Nylon 6.6) for Temperatures up to 85 Degrees Celsius (185 F) for Indoor Applications, Length of 334.57mm (13.172 Inches), Width of 6.86mm (0.27 Inch), Thickness of 1.52mm (0.06 Inch), Tensile Strength Rating of 534 Newtons (120 Pounds), Bulk Pack

**North American Specifications (UNSPSC)**

UNSPSC	39121703 Cable ties
IGCC	5034 Cable ties
Type	Detectable
Width	0.27 in ; 7 mm
Length	13.4 in ; 340 mm
Thickness	0.06 in ; 1.52 mm
Material	Nylon/Polyamide 6.6
Color	Blue
Lock Mechanism	Stainless Steel Barb
Tensile Strength	120 pounds ; 540 newtons

**European Specifications (ETIM)**

ETIM	EC000046 Cable tie
Band width	6.86mm
Length belt/tape/tie	334.57mm
Tie thickness	1.52mm
Min. holding force	534N
Model	Internal toothing
Band closure	Steel nose
Material	Plastic
Material quality	Polyamide PA
Surface protection	Untreated
Halogen free	Y
Colour	Blue
Transparent	N
Reflective (fluorescent)	N
Text strip	None
Solvable fastener	N
MIL approval	N

**Packaging**

Inner Quantity	500
Inner Dimensions (inches)	14x20x1
Outer Quantity	1000
Outer Dimensions (inches)	15.25x9.5x5
Weight Uom	11.5 lbs. per 1000