



Catalog Number: TY29M-6
Product ID: 7TCG009370R0036
UPC Number: 78621090045
EAN Number: 05414363063773
Status: A



High Performance Cable Tie, Blue Color Nylon 6.6, Length of 770mm (30.3 Inches) for Bundle Diameter up to 229mm (9.02 Inches), Width of 6.9mm (0.27 Inch), Tensile Strength Rating of 534 Newtons (120 Pounds), Operating Temperature of -60 Degrees Celsius (-76 F) to 85 Degrees Celsius (185 F)

- 316 stainless steel barb is corrosion resistant and provides greater longevity

Actual

North American Specifications (UNSPSC)

UNSPSC	39121703 Cable ties
IGCC	5034 Cable ties
Type	High Performance
Standard	UL E49405
Width	0.27 in ; 6.9 mm
Length	30.3 in ; 770 mm
Thickness	0.06 in ; 1.5 mm
Bundle Diameter	Max 9.02 in ; Max 229 mm
Material	Nylon/Polyamide 6.6
Color	Blue
Lock Mechanism	Stainless Steel Barb
Tensile Strength	120 pounds ; 534 newtons

European Specifications (ETIM)

ETIM	EC000046 Cable tie
Band width	6.93mm
Length belt/tape/tie	770.61mm
Tie thickness	1.52mm
Max. bundle diameter	229mm
Min. holding force	534N
Operating temperature	-40-+85°C
Model	Internal toothing
Band closure	Steel nose
Material	Plastic
Material quality	Polyamide PA
Surface protection	Untreated
UV-stable acc. ASTM D6779	N
Halogen free	Y
Colour	Blue
Transparent	N
Reflective (fluorescent)	N
Text strip	None
Solvable fastener	N
VG approval	N
MIL approval	Y
UL approval	Y

Packaging

Outer Quantity	500
Outer Dimensions (inches)	33.1x9.4x4.9
Weight Uom	2.25 lbs. per 100

Documents / Support Tools

Technical Drawing / Data Sheet	TDS000487
--------------------------------	-----------

