



Representative

Catalog Number: TY46M-3
Product ID: 7TAG009510R0020
UPC Number: 78621084552
EAN Number: 05414363163961
Status: A

Identification Cable Tie, Orange Polyamide (Nylon 6.6) for Temperatures up to 85 Degrees Celsius (185 F) for Indoor Applications, UL/EN/CSA62275 Type 2/21S Rated for AH-2 Plenum and as a Flexible Cable and Conduit Support, Length of 184.15mm (7.25 Inches), Width of 4.81mm (0.19 Inches), Thickness of 1.41mm (0.055 Inches), Tensile Strength Rating of 220 Newtons (50 pounds), Marking Pad Size of 12.7mm (0.50 Inches) x 26.99mm (1.062 Inches)

North American Specifications (UNSPSC)

| | |
|------------------|-------------------------|
| UNSPSC | 39121703 Cable ties |
| IGCC | 5040 I.D. Ties |
| Type | Identification |
| Standard | UL E49405 |
| Width | 0.19 in ; 4.81 mm |
| Length | 7.25 in ; 184.15 mm |
| Thickness | 0.055 in ; 1.4 mm |
| Material | Nylon/Polyamide 6.6 |
| Color | Orange |
| Lock Mechanism | Stainless Steel Barb |
| Tensile Strength | 50 pounds ; 220 newtons |

European Specifications (ETIM)

| | |
|--------------------------|--------------------|
| ETIM | EC000046 Cable tie |
| Band width | 4.81mm |
| Length belt/tape/tie | 184.15mm |
| Tie thickness | 1.41mm |
| Min. holding force | 220N |
| Model | Internal toothing |
| Band closure | Steel nose |
| Material | Plastic |
| Material quality | Polyamide PA |
| Surface protection | Untreated |
| Halogen free | Y |
| Colour | Orange |
| Transparent | N |
| Reflective (fluorescent) | N |
| Solvable fastener | N |
| MIL approval | N |
| UL approval | Y |

Packaging

| | |
|---------------------------|--------------------|
| Inner Quantity | 1000 |
| Inner Dimensions (inches) | 18x4x14 |
| Outer Quantity | 10000 |
| Outer Dimensions (inches) | 19x14x13 |
| Weight Uom | 0.63 lbs. per 1000 |

