



Representative

**Catalog Number:** TY46MD-2  
**Product ID:** 7TAG009510R0026  
**UPC Number:** 78621087539  
**EAN Number:** 05414363064930  
**Status:** A

Identification Cable Tie - Double Strap Configuration, Red Polyamide (Nylon 6.6) for Temperatures up to 85 Degrees Celsius (185 F) for Indoor Applications, UL/EN/CSA62275 Type 2/21S Rated for AH-2 Plenum and as a Flexible Cable and Conduit Support, Length of 184.15mm (7.25 Inches), Width of 4.81mm (0.19 Inches), Thickness of 1.41mm (0.055 Inches), Tensile Strength Rating of 220 Newtons (50 pounds), Marking Pad Size of 30.1mm (1.185 Inches) x 26.99mm (1.062 Inches)

**North American Specifications (UNSPSC)**

|                  |                         |
|------------------|-------------------------|
| UNSPSC           | 39121703 Cable ties     |
| IGCC             | 5040 I.D. Ties          |
| Type             | Identification          |
| Width            | 0.19 in ; 4.81 mm       |
| Length           | 7.25 in ; 184.15 mm     |
| Thickness        | 0.055 in ; 1.4 mm       |
| Material         | Nylon/Polyamide 6.6     |
| Color            | Red                     |
| Lock Mechanism   | Stainless Steel Barb    |
| Tensile Strength | 50 pounds ; 220 newtons |

**European Specifications (ETIM)**

|                          |                    |
|--------------------------|--------------------|
| ETIM                     | EC000046 Cable tie |
| Band width               | 4.81mm             |
| Length belt/tape/tie     | 184.15mm           |
| Tie thickness            | 1.41mm             |
| Min. holding force       | 220N               |
| Model                    | Internal toothing  |
| Band closure             | Steel nose         |
| Material                 | Plastic            |
| Material quality         | Polyamide PA       |
| Surface protection       | Untreated          |
| Halogen free             | Y                  |
| Colour                   | Red                |
| Transparent              | N                  |
| Reflective (fluorescent) | N                  |
| Solvable fastener        | N                  |
| MIL approval             | N                  |
| UL approval              | Y                  |

**Packaging**

|                           |                    |
|---------------------------|--------------------|
| Inner Quantity            | 500                |
| Outer Quantity            | 1000               |
| Outer Dimensions (inches) | 12.8x10.5x8.1      |
| Weight Uom                | 6.25 lbs. per 1000 |