



**Catalog Number:** TY46MT-4  
**Product ID:** 7TAG009510R0034  
**UPC Number:** 78621071423  
**EAN Number:** 05414363065029  
**Status:** A



Identification Cable Tie - Triple Strap Configuration, Yellow Polyamide (Nylon 6.6) for Temperatures up to 85 Degrees Celsius (185 F) for Indoor Applications, UL/EN/CSA62275 Type 2/21S Rated for AH-2 Plenum and as a Flexible Cable and Conduit Support, Length of 184.15mm (7.25 Inches), Width of 4.81mm (0.19 Inches), Thickness of 1.41mm (0.055 Inches), Tensile Strength Rating of 220 Newtons (50 pounds), Marking Pad Size of 46.02mm (1.815Inches) x 26.99mm (1.062 Inches)

Representative

**North American Specifications (UNSPSC)**

UNSPSC	39121703 Cable ties
IGCC	5040 I.D. Ties
Type	Identification
Standard	UL E49405
Width	0.19 in ; 4.81 mm
Length	7.25 in ; 184.15 mm
Thickness	0.055 in ; 1.4 mm
Material	Nylon/Polyamide 6.6
Color	Yellow
Lock Mechanism	Stainless Steel Barb
Tensile Strength	50 pounds ; 220 newtons

**European Specifications (ETIM)**

ETIM	EC000046 Cable tie
Band width	4.81mm
Length belt/tape/tie	184.15mm
Tie thickness	1.41mm
Min. holding force	220N
Model	Internal toothing
Band closure	Steel nose
Material	Plastic
Material quality	Polyamide PA
Surface protection	Untreated
Halogen free	Y
Colour	Yellow
Transparent	N
Reflective (fluorescent)	N
Solvable fastener	N
MIL approval	N
UL approval	Y

**Packaging**

Inner Quantity	500
Outer Quantity	1000
Weight Uom	8.13 lbs. per 1000